

CH - CA and MA CENTRAL LEVER


inserts		page:
CDD	42 poles + ⊕	78
CDS	18 poles + ⊕	-
CDSH	18 poles + ⊕	87
CNE	10 poles + ⊕	111
CSE	10 poles + ⊕	-
CSH	10 poles + ⊕	111
CSH S	10 poles + ⊕	123
CCE	10 poles + ⊕	131
CMSH	3+2 (aux) poles + ⊕	136
CMCE	3+2 (aux) poles + ⊕	137
CSS	10 poles + ⊕	149
CT, CTSE (16A) *)	10 poles + ⊕	161
CQE	18 poles + ⊕	169
CX	8/24 poles + ⊕	194
MIXO	3 modules	262 - 317

*) can be used only in bulkhead mounting housings

bulkhead mounting housings
for central leversurface mounting housings,
with two entries, for central lever

description	part No.	part No.	entry Pg	part No.	entry M
bulkhead mounting with pegs	CHI 10 YC				
surface mounting, high construction, with pegs		CAP 10 YC229	29x2	MAP 10 YC232	32x2

panel cut-out for bulkhead mounting housings




- ☒ Even when coding is not required, it is recommended to use CRM and CRF pins with CD and CDD inserts and CRM CX and CRF CX pins with MIXO inserts to reduce movements when fitting and removing the connectors and to avoid contact damages.

Within this scope, the DIN 43 652 standard requires a maximum angular longitudinal fluctuation of $\pm 5^\circ$.

CHI YC



CAP YC and MAP YC



CAUS

Type
4/4X/12

